

# Corrugated Plate Separator (CPS) For Oil/Solids Removal

## MORE THAN A WATER TREATMENT COMPANY, AN ESTABLISHED LEADER IN OIL/WATER SEPARATION

Corrugated Plate Separators (CPS) provide economical and effective removal of oil and solids from wastewater by gravity, in a smooth, efficient automatic flow.

With more than 3,000 installations in operation, this proven design has no moving parts and provides consistent operating results for simple and better separation.

### CORRUGATED PLATE INTERCEPTOR

At the heart of the CPS is the Corrugated Plate Interceptor (CPI) plate pack.

The plate pack design minimizes the distance a free oil droplet must rise before coming into contact with other oil droplets.

This design ensures that the oil droplets coalesce on the undersides of the corrugated plates, facilitating the free oil removal process.

# SIEMENS

### COMPACT, EFFICIENT DESIGN

The configuration and number of plates of the CPS units provide enough effective area for free oil removal down to 15 ppm and 60 micron removal.

Since the plates are arranged parallel to each other with a 3/4-inch spacing, the separator is able to tolerate up to 1000 ppm total suspended solids without effecting the effluent quality.


Typically, these units are one-fifth the size of an in-ground API separator, and produce a finer effluent quality.

### FEATURES AND BENEFITS

- Better effluent quality - removes free oil droplets 60 microns or larger
- Superior solids handling - tolerates 1000 ppm total suspended solids
- Low maintenance design-no moving parts
- Quality construction - design meets API standards



# Corrugated Plate Separator (CPS) For Oil/Solids Removal



## OPERATING PROCESS

Oily water enters the CPS unit to the influent receiving compartment. Here, the velocity is slowed and the flow is directed into the quiescent zone above the CPI pack(s). Gross, free oil droplets rise, and the flow containing residual small free droplets and solids particles enters the CPI in a laminar flow condition.

The CPI pack is uniquely designed to increase the separation surface area by using a series of parallel plates, arranged to allow small, free oil droplets to coalesce and separate from the carrier fluid. Separation is based on the differences in the specific gravities of the fluids and the liquid temperature.

Separated oil rises to the peaks of the corrugations in the parallel plates, then moves upward along these peaks to the top of the pack. As the separated oil is diverted to the top of the separator, it is protected from the flow entering the CPI by a gutter.

At the top of the unit, the separated oil forms a layer and is skimmed by an adjustable trough or weir. The clean effluent flows upward through the clear effluent compartment, then over the adjustable effluent weir and out of the separation unit.



*Prefabricated CPI plate rack, designed for easy removal as an assembly.*

Model No.	Approx. Flow Rate	
	GPM	BPD
800.10	10	343
800.25	60	2,057
800.50	125	4,286
801	250	8,571
802	500	17,143
803	750	25,714
824	1,000	34,286
826	1,500	51,429
8210.00	2,500	85,714

Separated solids in the CPI pack flow down the valleys of the corrugations to the bottom of the CPI pack. Another gutter shields them from the flow leaving the plate pack compartment. The use of a down-flow pack configuration ensures the entire water phase passes through the plate pack.

Because the pack is positioned at a 45° incline, separation is enhanced and the risk of plugging the media is minimized.

Test units are available for on-site use.

The information provided in this literature contains merely general descriptions or characteristics of performance which in actual case of use do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of the contract.

Siemens  
Water Technologies  
411 Commercial Parkway  
Broussard, LA 70518  
337.837.3071 phone  
337.837.9908 fax  
www.siemens.com/water

ZP-CPS-DS-0307  
monosep.water@siemens.com

©2007 Siemens Water Technologies Corp.  
Subject to change without prior notice.